

---

# cDAQ-9173

# Specifications

---

Ihr NI-Partner:



**AMC – Analytik & Messtechnik GmbH Chemnitz**

Heinrich-Lorenz-Str. 55    Tel.: +49/371/38388-0  
09120 Chemnitz    Fax: +49/371/38388-99  
E-Mail: [info@amc-systeme.de](mailto:info@amc-systeme.de)    Web: [www.amc-systeme.de](http://www.amc-systeme.de)



Integration  
Partner

SYSTEM INTEGRATOR

2025-08-05



# Contents

cDAQ-9173 Specifications ..... 3

# cDAQ-9173 Specifications

## cDAQ-9173 Specifications

These specifications apply to the cDAQ-9173.

### Revision History

Version	Date changed	Description
379135A-01	March 2025	Initial release.

### Looking For Something Else?

For information not found in the specifications for your product, such as operating instructions, browse ***Related Information***.

#### Related information:

- [cDAQ-9170/9173/9177 User Manual](#)
- [Software and Driver Downloads](#)
- [Dimensional Drawings](#)
- [Product Certifications](#)
- [Letter of Volatility](#)
- [Discussion Forums](#)
- [NI Learning Center](#)

### Definitions

***Warranted Specifications*** describe the performance of a model under stated operating conditions and are covered by the model warranty.

***Characteristics*** describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- **Typical**—describes the performance met by a majority of models.

- **Nominal**—describes an attribute that is based on design, conformance testing, or supplemental testing.

Values are **Typical** unless otherwise noted.


## Conditions

Specifications are valid at 25 °C unless otherwise noted.

## cDAQ-9173 Front Panel

Refer to the front panel diagram to understand the connectors, LEDs, and other features of the cDAQ-9173.

Figure 2. cDAQ-9173 Front Panel




1. POWER, STATUS, and ACTIVE LEDs
2. USB-C Port, with strain relief
3. Power Connector
4. Module Slots
5. Chassis Grounding Screw

## Physical Characteristics

Weight (unloaded)	603 g (21.27 oz)
-------------------	------------------

Dimensions (unloaded)	161.70 mm × 89.61 mm × 59.70 mm (6.366 in. × 3.528 in. × 2.350 in.)
<b>USB connector securement</b>	
USB securement type	Jackscrew provided on locking USB cable (part number 758787-01 or 769493-01)
Torque for jackscrew	0.41 N · m (3.6 lb · in.)
<b>Chassis ground</b>	
Gauge	1.31 mm <sup>2</sup> (16 AWG) or larger wire
Torque for ground screw	0.76 N · m (6.7 lb · in.)

Figure 3. cDAQ-9173 Dimensions



## Analog Input

Table 1. Analog Input

Input FIFO size	127 samples per slot
Maximum sample rate <sup>1</sup>	Determined by the C Series module or modules
Timing accuracy <sup>2</sup>	50 ppm of sample rate
Timing resolution	12.5 ns
Number of channels supported	Determined by the C Series module or modules

1. Performance dependent on type of installed C Series module and number of channels in the task.
2. Does not include group delay. For more information, refer to the documentation for each C Series module.

## Analog Output

Table 2. Number of channels supported (hardware-timed task)

Regeneration	Channels Supported
Onboard regeneration	16
Non-regeneration	Determined by the C Series module or modules

Table 3. Number of channels supported (non-hardware-timed task)

Channels supported	Determined by the C Series module or modules
--------------------	--

Table 4. Maximum update rate

Onboard regeneration	1.6 MS/s (multi-channel, aggregate)
Non-regeneration	Determined by the C Series module or modules

Table 5. Analog Output Timing

Timing accuracy	50 ppm of sample rate
Timing resolution	12.5 ns

Table 6. Output FIFO size

Onboard regeneration	8,191 samples shared among channels used
Non-regeneration	127 samples per slot

Table 7. Analog Output Waveform

AO waveform modes	<p>Non-periodic waveform,</p> <p>periodic waveform regeneration mode from onboard memory,</p> <p>periodic waveform regeneration from host buffer including dynamic update</p>
-------------------	---

## Digital Waveform Characteristics

Table 8. Waveform acquisition (DI) FIFO

Parallel modules	127 samples per slot per slot
------------------	-------------------------------

Table 9. Waveform generation (DO) FIFO

Parallel modules	2,047 samples per slot per slot
------------------	---------------------------------

Table 10. Digital input sample clock frequency

Streaming to application memory	System-dependent
Finite	0 MHz to 10 MHz

Table 11. Digital output sample clock frequency

Streaming from application memory	System-dependent
Regeneration from FIFO	0 MHz to 10 MHz
Finite	0 MHz to 10 MHz

Table 12. Digital waveform timing

Timing accuracy	50 ppm
-----------------	--------

## General-Purpose Counters/Timers

Number of counters/ timers	4
Resolution	32 bits
Counter measurements	Edge counting, pulse, semi-period, period, two-edge separation, pulse width

Position measurements	X1, X2, X4 quadrature encoding with Channel Z reloading; two-pulse encoding
Output applications	Pulse, pulse train with dynamic updates, frequency division, equivalent time sampling
Internal base clocks	80 MHz, 20 MHz, 100 kHz
External base clock frequency	0 MHz to 20 MHz
Base clock accuracy	50 ppm
Output frequency	0 MHz to 20 MHz
Inputs	Gate, Source, HW_Arm, Aux, A, B, Z, Up_Down
Routing options for inputs	Any module PFI, chassis PFI, analog trigger, many internal signals
FIFO	Dedicated 127-sample FIFO

## Frequency Generator

Table 13. Frequency generator

Number of channels	1
Base clocks <sup>3</sup>	20 MHz, 10 MHz, 100 kHz

3. Base clocks can be synchronized with other chassis using the network synchronization feature.

Divisors	1 to 16 (integers)
Base clock accuracy	50 ppm

# Module PFI Characteristics

Table 14. Module PFI Characteristics

Functionality	Static digital input, static digital output, timing input, and timing output
Timing output sources <sup>4</sup>	Many analog input, analog output, counter, digital input, and digital output timing signals
Timing input frequency	0 MHz to 20 MHz
Timing output frequency	0 MHz to 20 MHz


# Digital Triggers

Table 15. Digital triggers

Source	Any module PFI terminal
Polarity	Software-selectable for most signals
Analog input function	Start Trigger, Reference Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase
Analog output function	Start Trigger, Pause Trigger, Sample Clock, Sample Clock Timebase
Counter/timer function	Gate, Source, HW_Arm, Aux, A, B, Z, Up_Down

# Module I/O States

At power-on	Module-dependent. Refer to the documentation for each C Series module.
-------------	--

 **Note** The cDAQ-9173 may revert the input/output of the modules to their power-on state when the USB cable is removed.

4. Actual available signals are dependent on type of installed C Series module.

## Power Requirements



**Caution** You must use a National Electric Code (NEC) Class 2 power source with the cDAQ-9173 chassis.



**Note** Some C Series modules have additional power requirements. For more information about C Series module power requirements, refer to the documentation for each C Series module.



**Note** Sleep mode for C Series modules is not supported in the cDAQ-9173.

Input voltage range	9 to 30 V
Maximum required input power	15 W
Power input connector	2 positions 3.5 mm pitch pluggable screw terminal with screw locks similar to Sauro CTMH020F8
Power input mating connector	Sauro CTF020V8, Phoenix Contact 1714977, or equivalent
Power consumption from USB, 4.10 to 5.25 V	500 $\mu$ A maximum

## Bus Interface

USB specification	USB 2.0 Hi-Speed
High-performance data streams	7
Data stream types available	Analog input, analog output, digital input, digital output, counter/timer input, counter/timer output, NI-XNET



**Note** When a session is active, CAN or LIN (NI-XNET) C Series modules use a total of two data streams regardless of the number of NI-XNET modules in the chassis.



**Note** If you are connecting the cDAQ-9173 to a USB hub, the hub must be externally powered.

## Environmental Characteristics

<b>Temperature</b>	
Operating	-20 °C to 55 °C
Storage	-40 °C to 85 °C
<b>Humidity</b>	
Operating	10% to 90% RH, noncondensing
Storage	5% to 95% RH, noncondensing

Ingress Protection	IP 40
Pollution Degree	2
Maximum altitude	5,000 m

## Shock and Vibration

To meet these specifications, you must panel mount the cDAQ-9173 system, use an NI locking USB cable, and affix ferrules to the ends of the terminal lines.

Operational shock	30 g peak, half-sine, 11 ms pulse
<b>Random vibration</b>	
Operating	5 to 500 Hz, 0.3g <sub>rms</sub>
Non-operating	5 to 500 Hz, 2.4g <sub>rms</sub>

Ihr NI-Partner: 

**AMC – Analytik & Messtechnik GmbH Chemnitz**

Heinrich-Lorenz-Str. 55    Tel.: +49/371/38388-0  
 09120 Chemnitz            Fax: +49/371/38388-99  
 E-Mail: info@amc-systeme.de    Web: www.amc-systeme.de



Integration  
Partner

SYSTEM INTEGRATOR